

### **Product Features**

- Sanitary 3-A qualified
- All stainless steel 316 construction
- Large 4-digit LCD display
- Alarm display on measurement error and low battery condition
- Battery powered, life 5 years minimum
- High accuracy Microprocessor Based
- Utilizes Pt-1000 Ohm RTD Class A element for temperature sensing
- Optional RTD output, 2, 3 or 4-wire
- Resolution 1/10 of a degree
- IP 67/NEMA 4X (Waterproof)
- Display in degree C or F
- Programming and calibration option available

## **Description**

The Intempco Sanitary DTG-LCD Series battery powered Digital Temperature Gauges, is a step above all competition, providing accurate and reliable electronic temperature indication. Because of the robust IP67 housing all stainless design, they offer protection against moisture and dust penetration. The DTG can be used as a direct replacement for Bi-Metal, Liquid Bulb and Glass Thermometers where no power is available and are a suitable replacement under mercury reduction programs.

All models are factory calibrated for maximum accuracy. The DTG's 4-digit 1/2" (12.7 mm) LCD display can be factory set in units of °C or °F. With resolution to a tenth of a degree, the DTG takes the guesswork out of reading dials and mercury columns. Models with the programming option can be re-calibrated by performing a one-point or two-point calibration using known temperature standards with Intempco's DTG programming kit. This is where the DTG leaves the competition behind. Calibration, display resolution and other features are all programmable. Powered by a high performance 3.6 V battery, this thermometer will provide a minimum of five years continuous operation before batteries require replacement.

DTGs may be ordered as panel mounting with either three-hole front flange or back flange, or as a direct mounting thermometer with rigid stem. The rigid probe is either of 1/4"(6.35mm) or 3/8"(0.375mm) diameter as standard but other diameters and materials are available. Probes with flexible extensions are also available. The DTG wetted parts are all fabricated from stainless steel 316L. The RTD element used is Pt-1000 standard accuracy to DIN IEC 60751 Class A. DTG can be made available with an additional RTD output. This feature allows a single process connection to be used for indication of temperature and for remote indication, recording, or controlling. The electrical connector, a flexible cable or a Micro-DC (M12) male plug, are made available from the stainless housing for the optional RTD output. Each DTG has the part number, range and serial number marked on the thermometer housing.

DTG's can be returned to the factory or an authorized service center for verification and calibration. NIST traceable calibration certificates are an available option.

If you require an accurate, stable and dependable battery powered digital thermometer, look no further. Model DTG is your solution. For additional information please visit us on the web at www.intempco.com or contact your local Authorized Intempco Distributor.




# **Application/ Process Notes**


- For sanitary 3A applications
- CIP/SIP
- Ideal replacement for bi-metal, liquid bulb and gas thermometers
- Suitable for Mercury Reduction Programs
- Resistant to water spray, moisture and vibration
- **Pharmaceutical**
- Food preparation
- Milk and dairy
- **Pasteurizers**
- Sterilizers

E1.0 www.intempco.com Rev. B-02062016





# **Custom Builder**



| BOX1<br>CODE | Model Range                            |
|--------------|--|
| CL           | Low Temp., display °C<br>-50 to 200 °C |
| FL           | Low Temp., display °F<br>-58/392 °F    |

| BOX 2<br>CODE | Output Type   |
|---------------|---|
| 0             | No Output   |
| А3            | Pt 100 Ohm @ 0°C (±0.15°C)<br>$\alpha$ = 0.00385 DIN EN 60751<br>Class A (±0.06%), 3-wire |
| Т3            | Pt1000 Ohm @ 0°C (±0.15°C)<br>α = 0.00385 DIN EN 60751<br>Class A (±0.06%), 3-wire        |

#### Notes:

- 1. DTGs are factory calibrated to an accuracy of ±0.25% of span or better.
- 2. Order **DTG-PKIT-3** to set-up, re-program and re-calibrate in the field.
- Select Connector/Cable Type from Box9 for optional RTD output.
- 4. Other RTD types available. Consult factory.

| BOX3<br>CODE | Probe Diameter " D " |
|--------------|----------------------|
| В            | 1/8"                 |
| 40           | 0.156" (4.0 mm)      |
| С            | 3/16"                |
| D            | 1/4"                 |

Other diameters available. Consult factory.

| BOX4<br>CODE Probe Material |                          |
|-----------------------------|--------------------------|
| S                           | Stainless steel 316/316L |

Other materials available. Consult factory.

| BOX5<br>CODE | Probe Length "L"                                 |
|--------------|--|
|              | In 0.1" increments<br>Ex.: <b>065</b> =6.5" long |

| BOX6 | Extension   |
|------|---|
| CODE | Length " C "  |
| N    | In 0.1" increments (2.0" Std.)<br>Ex.: <b>N20</b> = 2.0" long |

| BOX7<br>CODE | Fixed Code |
|--------------|------------|
| 0            | Fixed Code |

| BOX8<br>CODE | Process Fitting Type/Size  |
|--------------|----------------------------|
| T12          | Hygienic clamp union, 1/2" |
| T34          | Hygienic clamp union, 3/4" |
|              |                            |

| BOX9<br>CODE | Connector Type<br>(Only Req. For Output Options) |
|--------------|--|
| 00           | No Connector                                     |
| MC           | M12 Micro-Male Connector,                        |

| BOX10<br>CODE | Extension Cable Length "H"<br>(Only Req. For Output Options) |
|---------------|--|
| N             | No Cable   |
| SB2           | Sanitary Molded Straight, 2 meters                           |
| BS5           | Sanitary Molded Straight, 5 meters                           |

| BOX11<br>CODE | Surface Finish                   |
|---------------|----------------------------------|
| SF            | 32μ-in (0.8μm) Ra max. or better |
| F1            | 20μ-in (0.5μm) Ra max. w/o EP    |
| F4            | 15μ-in (0.4μm) Ra max. with EP   |

| BOX12<br>CODE | Options   |
|---------------|---|
| N             | No Options  |
| C1            | Calibration certificate, NIST traceable, 1 point, 0°C (32°F)                                |
| C2            | Calibration certificate,<br>NIST traceable, 2 points,<br>0.0°C (32.0°F) & 100.0°C (212.0°F) |
| C3            | Calibration certificate,<br>NIST traceable, specify 3-points                                |

E2.0 www.intempco.com Rev. B-02062016



## **Technical Specifications**

Sensing Element: RTD, Type Pt1000 Ohm, Class A

Measuring Temperature Ranges : −50 °C to 200 °C (−58 °C to 392 °F) or −200 °C to 600 °C (−328 °F to 1112 °F)

depending model.

Accuracy :  $\pm (0.2 + 0.002 \times |T|)$  °C, std. factory,

 $\pm (0.36 + 0.002 \times |T-32|)$  °F, std. factory,  $\pm (0.2 + 0.001 \times |T|)$  °C, option,  $\pm (0.36 + 0.001 \times |T-32|)$  °F, option

For high accuracy measurement see manual

Refresh Rate: 3 seconds

Display: 4-digit LCD, 1/2" high (12.7 mm), decimal point selectable by software

Display Resolution :See table 1RFI effect :1 % or less typicalTemp. Effect :<0.01 % FS/°C</th>

 Ambient Temp. Range :
 0 °C to 50 °C (32 °F to 122 °F)

 Storage Temp. Range :
 -20 °C to 70 °C (-4 °F to 158 °F)

Max. Pressure:500 PSIG (on probe)Housing Material:Stainless steel 316

Probe Material: Stainless steel 316 standard

Standard Surface Finish: Code "SF"Maximum Ra of 32 μ-in (0.8 μm) or better as per 3-A 74-06 Sanitary onlyPharmaceutical Surface Finish: Code "F1"Per ASME BPE 2014 SF-1 20 μ-in (0.5 μm) Ra max. without electro polishPharmaceutical Surface Finish: Code "F4":Per ASME BPE 2014 SF-4 15 μ-in (0.4 μm) Ra max. with electro polish

Cable Materials: PVC, Silicone, Teflon®, Teflon® with SS armor covered with polyolefin or Teflon® shrink

Weight: 350 grams (12 ounces)

**Environmental Protection :** NEMA 4X/IP 67

Power: Lithium Battery (3.6 V)

Battery Life: 5 years min. in continuous mode

Electrical Connection: Micro-DC male plug or cable (with optional outputs only)

RTD Output Option: RTD, Type Pt100 or Pt1000 Ohm, 3-wire, Class A DIN IEC 60715

Communication Option: Communication option allows qualified users to calibrate, change measuring units and

resolution. DTG-PKIT-3 required, order separately.

**Shipping Volume:** Imperial Volume = 3.5"W X 3"H X (4.7" + L "of probe)

Metric Volume = 9.0 cm W X 8 cm H X (12 cm + Lcm of probe)

#### Table 1: Display Resolution

| Model Range                           | Factory Settings |                | Optional Settings |                 |         |                |
|---------------------------------------|------------------|----------------|-------------------|-----------------|---------|----------------|
|                                       | Setting          | Viewable Range | Setting           | Viewable Range  | Setting | Viewable Range |
| -50°C to 200°C<br>(-58°F to 392°F)    | 0.1              | -58.0 to 392.0 | 0.01              | -58.00 to 99.99 | 1       | -58 to 392     |
| -200°C to 600°C<br>(-328°F to 1112°F) | 1                | -328 to 1112   | 0.01              | -99.99 to 99.99 | 1       | -328 to 1112   |

Teflon® is a registered trademark of E.I. du Pont de Nemours and Company.

### **Installation Considerations**

Installation requirements of the DTG are similar to those of the temperature sensor assemblies with a head mounted hockey puck transmitter and display. If the temperature of the electronics in the housing exceeds 50 °C, permanent damage to the DTG will occur. In all applications, especially when they exceed 200 °C, careful attention must be placed on correct installation. For these applications, a remote probe wall mount unit or remote probe panel mount unit, may be a better choice. It is the installer's, customer's and/or end user's responsibility to make sure that this over exposure to temperature does not occur due to improper installation.

Rev. B-02062016 www.intempco.com | E3.0